

GainMaker® Line Extender 1 GHz with 55/70 MHz Split

Description

The GainMaker® Broadband Amplifier Platform includes a variety of RF amplifiers that address the divergent needs of today's broadband networks. All GainMaker amplifiers provide superior 2-way performance and reliability combined with a user-friendly layout. All share common plug-in accessories and perform to 1 GHz in the forward path. The Line Extenders in this family provide a single forward RF output port while the System Amplifiers provide multiple forward RF output ports.

The GainMaker Line Extender modules have increased gain and are mechanically compatible with previous Line Extender II and III housing bases, often enabling upgrade to higher bandwidth with no re-spacing or re-splicing. The DC power supply is modular and located in an updated housing lid for easy access. All GainMaker Line Extender modules are factory configured with reverse amplifier, diplex filters, forward interstage pads and interstage equalizer, to ensure optimal performance. For output level control over temperature, optional configurations additionally include either single-pilot Automatic Gain Control (AGC) or a Thermal compensation circuit.



The GainMaker Line Extender has a single forward RF output port and is ideally suited for providing high (bridger) level RF in the feeder network.


Features

- Common RF test points for forward output and reverse injection simplify reverse balancing
- Increased forward gain
- GaAsFET gain block technology for improved distortion and lower noise figure
- Fixed value plug-in accessories are common to all GainMaker products
- 60 and 90 volt AC powering capability
- Optional Power Pack kit allows quick field upgrade to 110V AC powering for indoor use
- 15 ampere current capacity (steady state) and 25 ampere surge survivability
- Optional 3-state reverse switch (on/off/-6 dB) allows noise and ingress troubleshooting (status monitoring required)
- AGC has Thermal backup, which eliminates disruptive RF output variation in the event of pilot loss
- Improved hum modulation
- Plug-in, self-contained diplex filters
- Modular high-efficiency power supply allows simplified maintenance
- Reverse input pad and RF test point for the reverse input port allow optimum reverse path design and alignment
- Directional coupler RF test points provide best accuracy
- Surge resistant circuitry ensures gain stage protection without fuses or other nuisance failure causing devices

GainMaker® - Line Extender - 5-55/70-1002 MHz



Block Diagram



GainMaker® - Line Extender - 5-55/70-1002 MHz

Specifications



General Station Performance	Units	Forward	Reverse	Notes
Pass Band	MHz	70-1002	5-55	
Amplifier Type	---	GaAs FET	PP	
Frequency Response	dB	± 0.5	± 0.5	
Auto Slope and Gain Range	dB	± 5	N/A	
Return Loss	dB	16	16	7
Max AC Through Current (continuous)	Amps	15	---	
Max AC Through Current (surge)	Amps	25	---	
Hum Modulation @ 12 A (over specified frequency range)	dB	70 (70-870 MHz) 60 (870-1002 MHz)	60 (5-10 MHz) 70 (11-55 MHz)	
Hum Modulation @ 15 A (over specified frequency range)	dB	65 (70-870 MHz) 60 (870-1002 MHz)	60 (5-10 MHz) 65 (11-55 MHz)	
Test Points (± 0.5 dB)	dB	-20	-20	
Reference Output Level @... 1002 MHz 870 MHz 750 MHz 650 MHz 550 MHz 70 MHz	dBmV	49.5 47.5 45.7 44.0 42.5 35.3	35 (@ 55 MHz) 35 (@ 5 MHz)	
Reference Output Tilt (70-1002 MHz)	dB	14.2	0	1

Forward Station Performance	Units	Manual	Thermal	AGC	Notes
Operational Gain	dB	37	32	31	2
Internal Tilt (± 0.5 dB)	dB	+9.1	+9.1	+9.1	3
Noise Figure @ 70 MHz	dB	6.0	7.5	7.5	2
Noise Figure @ 1002 MHz	dB	7.0	7.0	7.0	2
64 PAL B/G Channels (CW) with digital					4
Composite Triple Beat	dB	82	80	80	
Cross Modulation	dB	74	74	73	5
Composite Second Order (high side)	dB	75	75	75	
64 PAL I Channels (CW) with digital					10
Composite Beat	dB	75	73	73	8
Cross Modulation	dB	76	73	72	5
42 CENELEC Channels (CW)					9
Composite Triple Beat	dBuV	114	113	113.5	
Cross Modulation	dBuV	112	110.5	111.5	5
Composite Second Order	dBuV	115	115	116	
78 NTSC Channels (CW) with digital					11
Composite Triple Beat	dB	81	79	79	
Cross Modulation	dB	76	73	72	5
Composite Second Order (high side)	dB	76	75	75	

Reverse Station Performance	Units	Notes
Operational Gain (minimum)	dB	19.5 6,7
Internal Tilt (± 0.5 dB)	dB	0 3
Noise Figure	dB	8 6,7
CENELEC Distortions		9
Discrete Third Order	dBuV	114
Discrete Second Order	dBuV	120
6 NTSC Channels (CW)		
Composite Triple Beat	dB	92
Cross Modulation	dB	80 5
Composite Second Order (high side)	dB	82

Unless otherwise noted, specifications reflect typical performance and are referenced to 68°F (20°C). Specifications are based upon measurements made in accordance with SCTE/ANSI standards (where applicable), using standard frequency assignments.

GainMaker® - Line Extender - 5-55/70-1002 MHz

Specifications



Station Delay Characteristics			
Forward (Chrominance to Luminance Delay)		Reverse (Group Delay in 1.5 MHz bandwidth)	
Frequency (MHz)	Delay (ns)	Frequency (MHz)	Delay (ns)
71.25 - 75.68	28	5.0 - 6.5	60
76.25 - 80.68	13	6.5 - 8.0	22
83.25 - 87.68	7	8.0 - 9.5	12
112.25 - 116.68	2	50.5 - 52.0	11
		52.0 - 53.5	15
		53.5 - 55.0	23

Station Powering Data															
GainMaker Line Extender	I _{DC} (Amps)			AC Voltage											
	@ 12V	@ 24V		90	85	80	75	70	65	60	55	50	45	40	35
Manual and Thermal	1.74	0	AC Current (A)	0.45	0.47	0.49	0.51	0.52	0.53	0.62	0.64	0.67	0.70	0.76	0.86
			Power (W)	27.0	27.0	26.9	26.9	26.9	26.9	26.9	26.9	27.0	27.1	27.2	27.4
AGC	1.74	0.1	AC Current (A)	0.48	0.51	0.52	0.54	0.55	0.57	0.66	0.68	0.71	0.75	0.82	0.92
			Power (W)	29.2	29.1	29.1	29.1	29.1	29.1	29.1	29.1	29.2	29.3	29.4	29.6
AGC with Status Mon. & Reverse Switch	1.9	0.1	AC Current (A)	0.51	0.54	0.56	0.57	0.59	0.60	0.71	0.73	0.76	0.80	0.88	0.98
			Power (W)	31.5	31.5	31.5	31.5	31.4	31.4	31.6	31.6	31.6	31.7	31.9	32.1

Data is based on stations configured for 2-way operation. AC currents specified are based on measurements made with typical CATV type ferro-resonant AC power supply (quasi-square wave), and standard GainMaker Line Extender power supply (12/24 V DC, pn 593020).

DC supply has a user configurable 30 V, 40 V, or 50 V AC under voltage lockout circuit. Default setting is 30 V. 40 V or 50 V AC under voltage lockout may be selected by changing the position of the lockout jumper.

Notes:

- Reference output tilt is specified as "LINEAR" tilt (as opposed to "cable" tilt).
- Forward Gain and Noise Figure measured with 0 dB input EQ and 1 dB input pad.
- Down tilt, the effect of cable, is represented by a (-). Up tilt, the effect of cable equalization, is represented by a (+). Forward internal tilt specified is primarily due to an on board equalizer and either a factory configured 9 dB (Manual and AGC stations) or 7.5 dB (Thermal station) plug-in interstage equalizer.
- Loaded with 64 PAL B/G CW carriers from 112-600 MHz. Digital refers to 600-1002 MHz loading with 45 QAM carriers at -6 dB relative to analog CW carrier levels.
- X-mod (@ 15.75 kHz) specified using 100% synchronous modulation and frequency selective measurement device.
- Reverse Gain and Noise Figure for station with 0 dB reverse input pad, 0 dB reverse output EQ, and 1 dB output pad.
- Reverse Operational Gain, Noise Figure, and Return Loss are specified without reverse switch option. If switch is installed, reduce Gain by 0.5 dB, increase Noise Figure by 0.5 dB, and decrease Return Loss by 1 dB.
- Measured and specified as Composite Beat.
- Tested per CENELEC Standard EN50083-3. RF output level at 1002 MHz is specified.
- Loaded with 64 PAL I CW carriers from 88-600 MHz. Digital refers to 600-1002 MHz loading with 45 QAM carriers at -6 dB relative to analog CW carrier levels.
- Loaded with 78 NTSC CW carriers from 77-550 MHz. Digital refers to 550-1002 MHz loading with 53 QAM carriers at -6 dB relative to analog CW carrier levels.

Environmental	
Operating Temperature Range	-40 to +140°F (-40 to +60°C)
Mechanical	
Housing Dimensions	297.2 mm L x 248.9 mm H x 170.2 mm D 11.7 in. L x 9.8 in. H x 6.7 in. D
Weight	
• Housing with power supply	3 lbs, 12 oz. (1.7 kg)
• Module	9 lbs, 4 oz. (4.2 kg)

Unless otherwise noted, specifications reflect typical performance and are referenced to 68°F (20°C). Specifications are based upon measurements made in accordance with SCTE/ANSI standards (where applicable), using standard frequency assignments.

GainMaker® - Line Extender - 5-55/70-1002 MHz



Ordering Information

The **GainMaker Ordering Matrix** provides ordering information for configured amplifier modules or stations. This page contains ordering information for required and optional accessories that are not included as part of a configured amplifier module or station. Consult your account representative or customer service representative for ordering assistance.

*The following **Required Accessories** must be ordered separately (not included via GainMaker Ordering Matrix):*

Required Accessories	Part Number
Plug-in Pads (attenuators) - Available in 0.5 dB steps from 0 to 20 dB 1 required for forward input 1 required for AGC, if applicable* 2 required for reverse (1 input, 1 output) *To determine AGC pad value, subtract 29 dB from the design value station RF output level at the AGC pilot frequency (applies to Line Extender only)	589693 (0 dB) sequentially thru 589734 (20.5 dB)
Plug-in Forward Equalizer - Available in 1.5 dB steps from 0 to 30 dB at 1002 MHz 1 required for forward input	4007228 (0 dB) sequentially thru 4007248 (30 dB)
Plug-in Reverse Equalizer – Available in 1 dB steps from 0 to 12 dB at 55 MHz 1 required for reverse output - unless design value is 0 dB (0 dB EQ is provided)	712719 (0 dB) and 712679 (1 dB) sequentially thru 712690 (12 dB)

*The following **Optional Accessories** may be ordered separately:*

Optional Accessories	Part Number
230 V AC Crowbar Surge Protector (plug-in, one per station)	715973
Plug-in Inverse Equalizer. Simulates cable equivalent tilts (creates tilt opposite that of equalizers). Use in place of forward input EQ as needed to maintain proper output tilt in short spaced locations. Available in 1.6 dB "cable equivalent" steps from 1.6 to 16.2 dB.	4007486 (1.6 dB) sequentially thru 4007495 (16.2 dB)
Long Reach Test Point Adapter	562580
Status Monitoring Transponder – * see GainMaker Status Monitoring Transponder Data Sheet	*

*The following **Housing Options** may be included with the product if ordered using the GainMaker Ordering Matrix. They may also be ordered separately.*

GainMaker Line Extender Housing - 1 required. Housing includes housing base, lid, wiring harness, and 12/24 V power supply #593020. All Housings have 15 amp capacity.	Part Number
• Uncoated housing <i>without</i> external test point access	593095
• Chromate Plated housing <i>without</i> external test point access	593093
• Uncoated housing <i>with</i> external test point access	593094
• Chromate Plated housing <i>with</i> external test point access	593092
GainMaker Line Extender Housing Upgrade Kit - 1 required if upgrading an existing LEI, LEII, or LE III housing to allow use of GainMaker Line Extender modules. Includes a GainMaker Line Extender housing lid, wiring harness, and 12/24 V power supply #593020.	
• Uncoated housing lid <i>without</i> external test point access	593087
• Painted housing lid <i>without</i> external test point access	593085
• Uncoated housing lid <i>with</i> external test point access	593086
• Painted housing lid <i>with</i> external test point access	593084
Power Pack Kit (for indoor 110 V AC powering) - Includes LE wall mount bracket, power supply with indicator light, power supply bracket, housing base, lid, wiring harness, power cord strain relief - * see GainMaker Power Pack Data Sheet	748997
Seizure Upgrade Kit - 1 required if upgrading an existing LEI or LEII housing base to allow use of GainMaker Line Extender Modules. Includes high current (15 amp) rated seizure screws and anvils.	548774



Scientific-Atlanta, the Scientific-Atlanta logo, and GainMaker are registered trademarks of Scientific-Atlanta, Inc. ROSA is a trademark of Scientific-Atlanta Europe NV. Specifications and product availability are subject to change without notice. © 2006 Scientific-Atlanta, Inc. All rights reserved.

Scientific-Atlanta, Inc.
1-800-722-2009 or 770-236-6900
www.scientificatlanta.com

Part Number 7006953 Rev A
March 2006